

DATE 2-8-66

| NUMBER         | NAME                              | P OR L |
|----------------|-----------------------------------|--------|
| *AS-2040-87 ND | FRONT CABINET ASSEMBLY            | L      |
| AS-2041-36 ND  | FRONT DOOR ASSEMBLY (SINGLE COIN) | L      |
| AS-2041-37 ND  | FRONT DOOR ASSEMBLY (DOUBLE COIN) | L      |
| AS-2041-38 ND  | FRONT DOOR ASSEMBLY (TRIPLE COIN) | L      |
| *AS-2042-56 ND | PANEL ASSEMBLY                    | L      |
| *AS-2043-54 ND | BACK CABINET ASSEMBLY             | L      |
| *AS-2044-63 ND | BACK CABINET INSERT ASSEMBLY      | L      |
| *AS-2216-43 ND | MOUNTING BOARD ASSEMBLY           | L      |
|                |                                   |        |
|                |                                   |        |
| *              | WIRE                              | P      |
| *              | CABLES                            | L      |
| *              | WOOD PARTS                        | P      |
| *              | MISCELLANEOUS MATERIALS           |        |
| *              | LOOSE PARTS                       |        |
|                |                                   |        |
|                |                                   |        |
|                |                                   |        |
|                |                                   |        |
|                |                                   |        |



DATE ISSUED

USED ON

#779

2-8-66

SHEET 1 of 1

|    | PART NO.    | ASSEM. NO. | REQ. | H | Per L | PART NAME                                      |                               |
|----|-------------|------------|------|---|-------|------------------------------------------------|-------------------------------|
| 1  |             |            |      |   |       |                                                |                               |
| 2  | M-106-1a    |            | 8    | P |       | Leg Bolt                                       |                               |
| 3  | M-163-4a    |            | 4    | P |       | Leg Adjuster                                   |                               |
| 4  | M-168-26a   |            | 2    | P |       | Ball                                           | (1-1/6")                      |
| 5  | M-1078-4 ND |            | 1    | P |       | Carton                                         |                               |
| 6  | M-1369a     |            | 2    | P |       | Nylock Set Screws                              |                               |
| 7  |             |            |      |   |       |                                                |                               |
| 8  | P-1637-1b   |            | 1    | P |       | Roll Pin                                       | 6676                          |
| 9  | P-801-263b  |            | 4    | P |       | Washer                                         | (Mtg. Back Cab to Front Cab.) |
| 10 | P-3089-35a  |            | 1    | L |       | Cash Box Cover                                 |                               |
| 11 | P-4052-2b   |            | 4    | L |       | Legs                                           |                               |
| 12 | P-1637-30b  |            | 1    | P |       | Roll Pin                                       | 6676                          |
| 13 |             |            | 1    | P |       | 1/8 Hex Key                                    | (Used on 1/4 Set Screw)       |
| 14 |             |            |      |   |       |                                                |                               |
| 15 | N3/816-1110 |            | 4    | P |       | Nut, 3/8                                       | (Leg Adjuster)                |
| 16 |             |            |      |   |       |                                                |                               |
| 17 |             |            |      |   |       |                                                |                               |
| 18 |             |            |      |   |       |                                                |                               |
| 19 |             |            | 4    | P |       | Bolt, #3/8-16 x 3-1/2" Lg.Hex Hd.Cap Less Nuts | (Mtg. Back Cab.)              |
| 20 |             |            |      |   |       |                                                |                               |
| 21 |             |            | 1    | P |       | Polyethelene Bag, 2" x 4"                      | (Open Narrow End)             |
| 22 |             |            |      |   |       |                                                |                               |
| 23 |             |            |      |   |       |                                                |                               |
| 24 | *W-1042-19d |            | 1    | L |       | Schematic Wiring Diagram                       |                               |
| 25 |             |            |      |   |       |                                                |                               |
| 26 |             |            |      |   |       |                                                |                               |
| 27 |             |            |      |   |       |                                                |                               |
| 28 |             |            |      |   |       |                                                |                               |
| 29 |             |            |      |   |       |                                                |                               |
| 30 | A-2790-25b  |            | 1    | L |       | CASH BOX ASSEMBLY                              |                               |
| 31 | M-1299a     |            | 1    | L |       | Handle                                         |                               |
| 32 | P-4277-3a   |            | 2    | L |       | Clamp                                          |                               |
| 33 | P-6074-71a  |            | 2    | L |       | Front & Back                                   |                               |
| 34 | P-6074-72b  |            | 1    | L |       | Side & Bottom                                  |                               |
| 35 | P-6074-73a  |            | 2    | L |       | Divider                                        | 6604                          |
| 36 |             |            |      |   |       |                                                |                               |
| 37 |             |            | 1    | P |       | Coin Machine Lubricant                         | (Tube) 6852                   |
| 38 |             |            |      |   |       |                                                |                               |
| 39 | AS-1115-1a  |            | 1    | L |       | LAMP HOLDER ASSEMBLY                           | (LISTED SEP)                  |
| 40 |             |            |      |   |       |                                                |                               |
| 41 | E-125-5a    |            | 1    | P |       | Lamp - #55                                     | 6676                          |
| 42 | E-125-22a   |            | 1    | P |       | Lamp - #44                                     | 6676                          |
| 43 | E-133-8a    |            | 1    | P |       | Fuse - 8 AMP                                   | 6676                          |
| 44 | E-133-10a   |            | 1    | P |       | Fuse - 10 AMP                                  | 6676                          |
| 45 | E-133-15a   |            | 1    | P |       | Fuse - 15 AMP                                  | 6676                          |
| 46 |             |            |      |   |       |                                                |                               |
| 47 |             |            |      |   |       |                                                |                               |
| 48 |             |            |      |   |       |                                                |                               |
| 49 |             |            |      |   |       |                                                |                               |
| 50 |             |            |      |   |       |                                                |                               |
| 51 |             |            |      |   |       |                                                |                               |
| 52 |             |            |      |   |       |                                                |                               |
| 53 |             |            |      |   |       |                                                |                               |



## PARTS LIST

NAME

CABLES

DATE ISSUED

USED ON

#779

2-8-66

SHEET 1 OF 2

|    | PART NO.      | ASSEM. NO. | REQ. | H | Por L                     | PART NAME              |             |
|----|---------------|------------|------|---|---------------------------|------------------------|-------------|
| 1  |               |            |      |   |                           |                        |             |
| 2  | *E-556-196 ND |            | 1    | L | MOUNTING BOARD CABLE      | (PER ENG. SAMPLE)      |             |
| 3  | E-103-9a      |            | 1    | P | Terminal                  |                        |             |
| 4  | E-107-2a      |            | 1    | P | Connector                 | (2 Pt. in Line Female) |             |
| 5  | E-126a        |            | 1    | P | Cord Set                  |                        |             |
| 6  | E-136-3a      |            | 1    | P | Connector                 | (3 Pt. in Line Female) |             |
| 7  | E-136-6a      |            | 1    | P | Connector                 | (6 Pt. in Line Female) |             |
| 8  | E-137-4a      |            | 2    | P | Connector                 | (4 Pt. Female)         |             |
| 9  | E-137-6a      |            | 1    | P | Connector                 | (6 Pt. Female)         |             |
| 10 | E-137-8a      |            | 1    | P | Connector                 | (8 Pt. Female)         |             |
| 11 | E-137-20a     |            | 1    | P | Connector                 | (20 Pt. Female)        |             |
| 12 | E-137-24a     |            | 1    | P | Connector                 | (24 Pt. Female)        | 6691        |
| 13 | E-139-14a     |            | 1    | P | Connector                 | (14 Pt. Male)          |             |
| 14 | E-139-18a     |            | 1    | P | Connector                 | (18 Pt. Male)          |             |
| 15 | E-139-22a     |            | 1    | P | Connector                 | (22 Pt. Male)          |             |
| 16 | E-140-1a      |            | 3    | P | Connector                 | (1 Pt. in Line Male)   |             |
| 17 | E-140-2a      |            | 3    | P | Connector                 | (2 Pt. in Line Male)   |             |
| 18 |               |            |      |   |                           |                        |             |
| 19 | E-136-2a      |            | 1    | P | Connector                 | (2 Pt. in Line Female) | (For German |
| 20 | E-140-1a      |            | 1    | P | Connector                 | (1 Pt. in Line Male)   | Games Only) |
| 21 |               |            |      |   |                           |                        |             |
| 22 |               |            |      |   |                           |                        |             |
| 23 |               |            |      |   |                           |                        |             |
| 24 | *E-556-197 ND |            | 1    | L | INSERT CABLE              | (PER ENG. SAMPLE)      |             |
| 25 | E-136-5a      |            | 1    | P | Connector                 | (5 Pt. in Line Female) | (Bell) 7096 |
| 26 | E-137-10a     |            | 1    | P | Connector                 | (10 Pt. Female)        |             |
| 27 | E-137-14a     |            | 1    | P | Connector                 | (14 Pt. Female)        |             |
| 28 | E-137-18a     |            | 1    | P | Connector                 | (18 Pt. Female)        |             |
| 29 | E-137-22a     |            | 2    | P | Connector                 | (22 Pt. Female)        |             |
| 30 | E-140-1a      |            | 10   | P | Connector                 | (1 Pt. in Line Male)   |             |
| 31 | E-140-2a      |            | 1    | P | Connector                 | (2 Pt. in Line Male)   |             |
| 32 | E-136-7a      |            | 1    | P | Connector                 | (7 Pt. in Line Female) | 7096        |
| 33 |               |            |      |   |                           |                        |             |
| 34 |               |            |      |   |                           |                        |             |
| 35 | *E-556-198 ND |            | 1    | L | PANEL CABLE               | (PER ENG. SAMPLE)      |             |
| 36 | E-139-20a     |            | 1    | P | Connector                 | (20 Pt. Male)          |             |
| 37 | E-139-24a     |            | 2    | P | Connector                 | (24 Pt. Male)          | 6691        |
| 38 |               |            |      |   |                           |                        |             |
| 39 |               |            |      |   |                           |                        |             |
| 40 |               |            |      |   |                           |                        |             |
| 41 | E-556-188 ND  |            | 1    | L | TILT FLIPPER SWITCH CABLE | (PER ENG. SAMPLE)      |             |
| 42 | E-139-8a      |            | 1    | P | Connector                 | (8 Pt. Male)           |             |
| 43 | M-175a        |            | 1    | P | Plumb Bob Wire            | (Tilt)                 |             |
| 44 | P-405-2a      |            | 2    | P | Soldering Terminal        | (Tilt)                 |             |
| 45 | SW-100-358a   |            | 1    | P | Switch                    | (Right Flipper)        |             |
| 46 | SW-200-130a   |            | 1    | P | Switch                    | (Left Flipper)         |             |
| 47 | AS-1588-1     |            | 1    | L | BALL TILT ASSEMBLY        | (LISTED SEP.)          |             |
| 48 |               |            |      |   |                           |                        |             |
| 49 |               |            |      |   |                           |                        |             |
| 50 |               |            |      |   |                           |                        |             |
| 51 |               |            |      |   |                           |                        |             |
| 52 |               |            |      |   |                           |                        |             |
| 53 |               |            |      |   |                           |                        |             |



## PARTS LIST

NAME

CABLES

Q.C.

DATE ISSUED

USED ON

#779

2-8-66

SHEET 2 OF 2

|    | PART NO.     | ASSEM. NO. | REQ. | H | Per L | PART NAME        |                        |
|----|--------------|------------|------|---|-------|------------------|------------------------|
| 1  |              |            |      |   |       |                  |                        |
| 2  | E-556-183 ND |            | 1    |   | L     | SOUNDER CABLE    | (PER ENG. SAMPLE)      |
| 3  | E-140-2a     |            | 1    |   | P     | Connector        | (2 Pt. in Line Male)   |
| 4  |              |            |      |   |       |                  |                        |
| 5  |              |            |      |   |       |                  |                        |
| 6  |              |            |      |   |       |                  |                        |
| 7  | E-556-209 ND | (As Req.)  | 1    |   | L     | FRONT DOOR CABLE | (PER ENG. SAMPLE) 8147 |
| 8  | E-139-6a     |            | 1    |   | P     | Connector        | (6 Pt. Male)           |
| 9  |              |            |      |   |       |                  |                        |
| 10 |              |            |      |   |       |                  |                        |
| 11 |              |            |      |   |       |                  |                        |
| 12 | E-556-210 ND | (As Req.)  | 1    |   | L     | FRONT DOOR CABLE | (PER ENG. SAMPLE) 8147 |
| 13 | E-139-6a     |            | 1    |   | P     | Connector        | (6 Pt. Male)           |
| 14 |              |            |      |   |       |                  |                        |
| 15 |              |            |      |   |       |                  |                        |
| 16 |              |            |      |   |       |                  |                        |
| 17 | E-556-211 ND | (As Req.)  | 1    |   | L     | FRONT DOOR CABLE | (PER END. SAMPLE) 8147 |
| 18 | E-139-6a     |            | 1    |   | P     | Connector        | (6 Pt. Male)           |
| 19 |              |            |      |   |       |                  |                        |
| 20 |              |            |      |   |       |                  |                        |
| 21 |              |            |      |   |       |                  |                        |
| 22 |              |            |      |   |       |                  |                        |
| 23 |              |            |      |   |       |                  |                        |
| 24 |              |            |      |   |       |                  |                        |
| 25 |              |            |      |   |       |                  |                        |
| 26 |              |            |      |   |       |                  |                        |
| 27 |              |            |      |   |       |                  |                        |
| 28 |              |            |      |   |       |                  |                        |
| 29 |              |            |      |   |       |                  |                        |
| 30 |              |            |      |   |       |                  |                        |
| 31 |              |            |      |   |       |                  |                        |
| 32 |              |            |      |   |       |                  |                        |
| 33 |              |            |      |   |       |                  |                        |
| 34 |              |            |      |   |       |                  |                        |
| 35 |              |            |      |   |       |                  |                        |
| 36 |              |            |      |   |       |                  |                        |
| 37 |              |            |      |   |       |                  |                        |
| 38 |              |            |      |   |       |                  |                        |
| 39 |              |            |      |   |       |                  |                        |
| 40 |              |            |      |   |       |                  |                        |
| 41 |              |            |      |   |       |                  |                        |
| 42 |              |            |      |   |       |                  |                        |
| 43 |              |            |      |   |       |                  |                        |
| 44 |              |            |      |   |       |                  |                        |
| 45 |              |            |      |   |       |                  |                        |
| 46 |              |            |      |   |       |                  |                        |
| 47 |              |            |      |   |       |                  |                        |
| 48 |              |            |      |   |       |                  |                        |
| 49 |              |            |      |   |       |                  |                        |
| 50 |              |            |      |   |       |                  |                        |
| 51 |              |            |      |   |       |                  |                        |
| 52 |              |            |      |   |       |                  |                        |
| 53 |              |            |      |   |       |                  |                        |



## PARTS LIST

NAME

MISCELLANEOUS MATERIALS

DATE ISSUED

4-15-66

USED ON

#779

SHEET 1 OF 1

|    | PART NO.    | ASSEM. NO. | REQ.    | H | Per L | PART NAME                         |                                         |
|----|-------------|------------|---------|---|-------|-----------------------------------|-----------------------------------------|
| 1  |             |            |         |   |       |                                   |                                         |
| 2  | E-110-2a    |            | 1       |   | P     | Convenience Outlet                | (Domestic Only)                         |
| 3  |             |            |         |   |       |                                   |                                         |
| 4  |             |            |         |   |       |                                   |                                         |
| 5  |             |            |         |   |       |                                   |                                         |
| 6  | M-469-303b  |            | As Req. |   | P     | Labels                            | (Standard)                              |
| 7  | M-469-378b  |            | As Req. |   | P     | Labels                            | (Misc.)                                 |
| 8  | *M-469-389b |            | As Req. |   | P     | Labels                            | (German)                                |
| 9  |             |            |         |   |       |                                   |                                         |
| 10 |             |            |         |   |       |                                   |                                         |
| 11 |             |            |         |   |       |                                   |                                         |
| 12 | WS8-8-510   |            | 4       |   | P     | R.H.W.S.                          | (Counter Support Brkt.)                 |
| 13 | WS8-20-510  |            | 2       |   | P     | R.H.W.S.                          | (Shipping Block)                        |
| 14 |             |            |         |   |       |                                   |                                         |
| 15 |             |            | 2       |   | P     | Stove Pipe Wire 7" Lg. 3/64 Dia.  | (Gang Mount) 8109                       |
| 16 |             |            |         |   |       |                                   |                                         |
| 17 | Sleeving    |            | As Req. |   | P     | C-2 Set High Grade Dbl.           | (#16 Ga. Yellow, Green, Blue, Gray, Red |
| 18 |             |            |         |   |       |                                   | (Brown & Black)                         |
| 19 | Sleeving    |            | As Req. |   | P     | C-2 Set High Grade Dbl.           | (#20 Ga. Yellow, Green, Blue, Gray, Red |
| 20 |             |            |         |   |       |                                   | (Brown & Black)                         |
| 21 |             |            |         |   |       |                                   |                                         |
| 22 |             |            |         |   |       |                                   |                                         |
| 23 | Sleeving    |            | As Req. |   | P     | Clear Extruded                    | #5                                      |
| 24 | Sleeving    |            | As Req. |   | P     | Clear Extruded                    | #6                                      |
| 25 | Sleeving    |            | As Req. |   | P     | Clear Extruded                    | #7                                      |
| 26 |             |            |         |   |       |                                   |                                         |
| 27 |             |            |         |   |       |                                   |                                         |
| 28 |             |            |         |   |       |                                   |                                         |
| 29 | Wire        |            | As Req. |   | P     | #18 Solid Tinned Copper           |                                         |
| 30 | Wire        |            | As Req. |   | P     | #24 Solid Tinned Copper           |                                         |
| 31 | Wire        |            | As Req. |   | P     | #20 Bare Braided                  |                                         |
| 32 |             |            |         |   |       |                                   |                                         |
| 33 |             |            |         |   |       |                                   |                                         |
| 34 |             |            | As Req. |   | P     | Masking Tape, 3/4" Wide           |                                         |
| 35 |             |            | As Req. |   | P     | #33 Black Plastic Electrical Tape |                                         |
| 36 |             |            |         |   |       |                                   |                                         |
| 37 |             |            |         |   |       |                                   |                                         |
| 38 |             |            | As Req. |   | P     | Solder                            |                                         |
| 39 |             |            |         |   |       |                                   |                                         |
| 40 |             |            |         |   |       |                                   |                                         |
| 41 |             |            | As Req. |   | P     | Tape "PERMACAL" #15-1" Wide       | (216' Per Roll)                         |
| 42 |             |            | As Req. |   | P     | Tape "GLASPUN" 3" Wide            | (300' Per Roll)                         |
| 43 |             |            |         |   |       |                                   |                                         |
| 44 |             |            |         |   |       |                                   |                                         |
| 45 |             |            |         |   |       |                                   |                                         |
| 46 |             |            | As Req. |   | P     | Lacing Twine #244 Type 500        | (Penn Nylon)                            |
| 47 |             |            |         |   |       |                                   |                                         |
| 48 |             |            |         |   |       |                                   |                                         |
| 49 |             |            |         |   |       |                                   |                                         |
| 50 |             |            |         |   |       |                                   |                                         |
| 51 |             |            |         |   |       |                                   |                                         |
| 52 |             |            |         |   |       |                                   |                                         |
| 53 |             |            |         |   |       |                                   |                                         |



DATE ISSUED

USED ON

#779

2-9-66

SHEET 1 of 1

|    | PART NO.       | ASSEM. NO. | REQ. | H | Per L | PART NAME                       |                                             |
|----|----------------|------------|------|---|-------|---------------------------------|---------------------------------------------|
| 1  |                |            |      |   |       |                                 |                                             |
| 2  | *CA-1128-32d   |            | 1    |   | P     | PANEL                           |                                             |
| 3  | C-665-5a       | (White)    | 3    |   | P     | Playboard Insert (Rollover)     | (Furnished to Grand)                        |
| 4  | C-667-1a       | (Red)      | 1    |   | P     | Playboard Insert (1" Dia.)      | (Furnished to Grand)                        |
| 5  | C-667-4a       | (Green)    | 1    |   | P     | Playboard Insert (1" Dia.)      | (Furnished to Grand)                        |
| 6  | C-667-5a       | (White)    | 16   |   | P     | Playboard Insert (1" Dia.)      | (Furnished to Grand)                        |
| 7  | C-668-5a       | (White)    | 9    |   | P     | Playboard Insert (3/4" Dia.)    | (Furnished to Grand)                        |
| 8  |                |            |      |   |       |                                 |                                             |
| 9  |                |            |      |   |       |                                 |                                             |
| 10 |                |            |      |   |       |                                 |                                             |
| 11 | *CA-1125-33 ND |            | 1    |   | P     | FRONT CABINET                   | (Same AS CA-1125-34d Except Screening) 8495 |
| 12 | M-108-1a       |            | 4    |   | P     | Tee Nut (3/8-16)                | (Furnished to Grand)                        |
| 13 | M-108-11a      |            | 4    |   | P     | Double Tee Nut (3/8-16)         | (Furnished to Grand)                        |
| 14 | M-108-18a      |            | 2    |   | P     | Tee Nut (5/16-18)               | (Furnished to Grand)                        |
| 15 |                |            |      |   |       |                                 |                                             |
| 16 |                |            |      |   |       |                                 |                                             |
| 17 |                |            |      |   |       |                                 |                                             |
| 18 | *CA-1127-27 ND |            | 1    |   | P     | BACK CABINET SPACER             | (Same as CA-1127-3a Except Screening)       |
| 19 |                |            |      |   |       |                                 |                                             |
| 20 |                |            |      |   |       |                                 |                                             |
| 21 |                |            |      |   |       |                                 |                                             |
| 22 | *CA-1134-31 ND |            | 1    |   | P     | BACK CABINET                    | (Same as CA-1134-11d Except Screening)      |
| 23 |                |            |      |   |       |                                 |                                             |
| 24 |                |            |      |   |       |                                 |                                             |
| 25 |                |            |      |   |       |                                 |                                             |
| 26 | CA-567-159b    | As Req.    | 1    |   | P     | FRONT DOOR (Triple)             | 8495                                        |
| 27 | CA-567-162b    | As Req.    | 1    |   | P     | FRONT DOOR (Single)             | 8495                                        |
| 28 | CA-567-163b    | As Req.    | 1    |   | P     | FRONT DOOR (Double)             | 8495                                        |
| 29 |                |            |      |   |       |                                 |                                             |
| 30 | *CA-1135-30d   |            | 1    |   | P     | BACK CABINET INSERT             |                                             |
| 31 |                |            |      |   |       |                                 |                                             |
| 32 |                |            |      |   |       |                                 |                                             |
| 33 | *CA-475-16a    |            | 1    |   | P     | Mounting Board                  |                                             |
| 34 |                |            |      |   |       |                                 |                                             |
| 35 |                |            |      |   |       |                                 |                                             |
| 36 | CA-952-1a      |            | 1    |   | P     | Brace (Panel)                   |                                             |
| 37 |                |            |      |   |       |                                 |                                             |
| 38 |                |            |      |   |       |                                 |                                             |
| 39 | CA-456-130a    |            | 1    |   | P     | Relay Mounting Board (2 Relay)  |                                             |
| 40 | CA-456-131a    |            | 1    |   | P     | Relay Mounting Board (5 Relay)  |                                             |
| 41 | CA-456-140a    |            | 1    |   | P     | Relay Mounting Board (15 Relay) |                                             |
| 42 |                |            |      |   |       |                                 |                                             |
| 43 |                |            |      |   |       |                                 |                                             |
| 44 | CA-610-28a     | Void       | 4    |   | P     | Block                           | 6858                                        |
| 45 | CA-610-32a     |            | 1    |   | P     | Block                           |                                             |
| 46 |                |            |      |   |       |                                 |                                             |
| 47 |                |            |      |   |       |                                 |                                             |
| 48 | CA-535-1a      |            | 1    |   | P     | Handle                          |                                             |
| 49 |                |            |      |   |       |                                 |                                             |
| 50 |                |            |      |   |       |                                 |                                             |
| 51 |                |            |      |   |       |                                 |                                             |
| 52 |                |            |      |   |       |                                 |                                             |
| 53 |                |            |      |   |       |                                 |                                             |



DATE 2-21-66

[illegible]